



+ CONNECTORS

CIRCULAR POWER CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

CPC 17-9 POSTED RECEPTACLE ASY

AMP | CPC

213826-1

TE Internal Number: 213826-1

Not EU RoHS Compliant

Not EU ELV Compliant

Product Type Connector Assembly

Connector System Wire-to-Board, Wire-to-Panel

Number of Positions 9

Housing Type Receptacle

Reverse Gender Reverse

[↓](#) **PRODUCT DRAWING**
English

[↓](#) **3D PDF**

DOCUMENTATION

Product Drawings

RECEPTACLE ASSEMBLY, POSTED, REVERSE SEX, SERIES 1, 17-9, CPC

PDF (TIFF AVAILABLE)

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Application Specification

Circular Plastic Connectors (CPC)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Connector Assembly

Connector System Wire-to-Board, Wire-to-Panel

Housing Type Receptacle

Contact Type Socket

Shell Type All Plastic

Configuration Features

Number of Positions 9

Number of Power Positions 0

Number of Signal Positions 9

Keying A

Contact Features

Reverse Gender Reverse

Mechanical Attachment

Panel Mount Retention Type Flange with Mounting Holes

Connector Mounting Type Panel

Mating Alignment With

Mating Retention With

Panel Mount Retention With

Mating Retention Type Threaded Coupling

Mating Alignment Type Keyed

Housing Features

Shell Size 17

UL Flammability Rating UL 94V-0

Dimensions

Assembly Length (in) 1.27

Usage Conditions

Sealed Condition Sealed

Fluid Resistance Immersion

Packaging Features

Packaging Quantity 24

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
