

213889-1 Product Details

[Share](#) | [Print](#) | [Email](#)


CPC (Circular Plastic) and Circular Metal-Shell Connectors

CPC RCPT, FLANGE MNT, SRS 5, 17-3

213889-1

TE Internal Number: 213889-1

Active

[View 3D PDF](#)

Product Highlights [View All](#)

- Housing
- Connector Style = Receptacle
- 3 Positions
- 0 Signal Positions
- 3 Power Positions

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Connector Type	Housing
Mount Angle	Straight
Shell Size [?]	17
PCB Mount Retention	Without
Shell Type [?]	All Plastic
Product Series [?]	Series 5
Thread Size [?]	15/16-20 UNEF-2A
Sealed [?]	No

Mechanical Attachment	
Mount [?]	Panel
Mating Retention Type	Threaded Coupling

Body Features	
Mount Style [?]	Flange with Mounting Holes

Contact Features	
Contact Type [?]	Socket
Reverse Gender [?]	Reverse

Housing Features	
Connector Style [?]	Receptacle
Mating Alignment Type	Keyed
Housing Material	Thermoplastic
Housing Color	Black

Configuration Features	
Number of Positions [?]	3
Number of Signal Positions [?]	0
Number of Power Positions [?]	3
Environmental Protection [?]	With
Reverse Numbering [?]	Without

Industry Standards	
VDE Tested [?]	No
RoHS/ELV Compliance [?]	RoHS compliant, ELV compliant
Lead Free Solder Processes [?]	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Environmental	
Fluid Resistance [?]	Immersion

Conditions for Usage	
Accepts Wire Insulation Diameter, Range (mm [in])	3.81 - 6.73 [0.150 - 0.265]

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)