

2-5161500 -0 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



2-5161500 -0

[Active](#)

2.5mm & 5mm Miniature Interconnection System - IDC (Mini - Match)

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Header
- ? Number of Positions = 20
- ? 2.50 mm Centerline
- ? Terminate To Printed Circuit Board
- ? PCB Mount Angle = Vertical

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [mini match make connector 3 -20 pos](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [PCB Layout](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Header
- ? Number of Positions = 20
- ? PCB Mount Angle = Vertical
- ? Color = Green

Body Related Features:

- ? Centerline (mm [in]) = 2.50 [0.098]
- ? Material Flammability Rating = UL 94V -0

Contact Related Features:

- ? Contact Material = Phosphor Bronze
- ? Contact Mating Area Plating Material = Tin

Housing Related Features:

- ? Housing Material = Thermoplastic Polyester

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Terminate To = Printed Circuit Board

Other:

- ? Brand = AMP