


281792-8 Product Details

 [Live Product Chat](#)




281792-8

TE Part Number: 281792-8

 [Active](#)

 [Add to Part List](#)

.100 AMPMODU Headers, Housings & Contacts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Housing
- Preloaded
- Number of Positions = 16
- Housing Type = Receptacle
- Contact Type = Receptacle

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Housing
- [Number of Positions](#) = 16
- [Mating Connector Lock](#) = Without
- Mating Polarization = Without
- Wire Insulation Diameter (mm [in]) = 1.00 [0.039]
- [Keyed](#) = No
- [Connector Series](#) = HE13 / HE14
- Wire Termination Type = Crimp, Insulation Displacement Crimp (IDC)

Mechanical Attachment:

- Preloaded = Yes

Body Related Features:

- [Housing Type](#) = Receptacle
- [Number of Rows](#) = Dual
- [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 [.100]
- [Wire Range \(mm \[AWG\]\)](#) = 0.08-0.15² [28-26]

Contact Related Features:

- Contact Type = Receptacle
- [Contact Mating Area Plating Material](#) = Tin
- Contact Material = Phosphor Bronze

Housing Related Features:

- [Housing Color](#) = Blue
- Housing Flammability Rating = UL 94V-0
- Housing Material = PBT - GF

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Terminate To](#) = Wire

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- Brand = AMP