


316998 -7 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



316998 -7

Active

1.27 [.050] Series II and Series III Connectors

[Converted to EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Mating Type = Receptacle
- ? Number of Positions = 50
- ? Terminate To Printed Circuit Board
- ? Right Angle Mount Angle
- ? Yes PCB Retention Feature

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [RECEPTACLE HDR ASS'Y\(3.1mm\) CHAMP.050 SERIES\(II\) FMS...](#) (PDF, Japanese)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [CHAMP.050 Series\(II\) Connector Wire to Board Type](#) (PDF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version B)
- ? [3D Model](#) (IGES, Version B)
- ? [3D Model](#) (STEP, Version B)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Mating Type](#) = Receptacle
- ? [Number of Positions](#) = 50
- ? [Mount Angle](#) = Right Angle
- ? [PCB Retention Feature](#) = Yes
- ? [Mating Connector Lock](#) = Without
- ? [Product Series](#) = Series II
- ? Color = Black
- ? Shell Material = Steel

Mechanical Attachment:

- ? [Panel Attachment](#) = Without
- ? Tine Plate Material = PBT

Termination Related Features:

- ? Termination (Solder) Post Length (mm [in]) = 3.10 [0.122]
- ? Solder Tail Contact Plating = Tin

Body Related Features:

- ? Centerline (mm [in]) = 1.27 [0.050]
- ? PCB Retention Method = Boardlock(s)
- ? Shell Plating = Nickel over Copper

Contact Related Features:

- ? [Contact Mating Area Plating](#) = Gold (12)
- ? Contact Material = Copper Alloy

Housing Related Features:

- ? [Housing Material Temperature](#) = Standard
- ? Housing Material = PBT
- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = AMP