


34846 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



34846

[Active](#)

Miscellaneous Terminals

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Shur-Plug
- ? Insulation Support
- ? Wire Range = 1.25 -2.00 ² [16-14] mm [AWG]
- ? Not For Use With Double Wire
- ? Copper Material

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [WIRE TERMINAL BUDGET, SHUR PLUG, WIRE SIZE: 16 14](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Shur -Plug
- ? [Insulation Support](#) = Insulation Support
- ? Material = Copper
- ? Finish = Tin
- ? Product Series = SHUR -PLUG
- ? Insulation Diameter (mm [in]) = 3.18 [.125] Max.

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 1.25 -2.00 ² [16-14]
- ? Double Wire = No

Contact Related Features:

- ? Bulb = Without

Configuration Related Features:

- ? Diode = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? Packaging Method = Loose Piece
- ? Packaging Quantity = Bulk

Other:

- ? Brand = AMP