

# 2.5MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK

✓ ACTIVE

[Buchanan](#) | [Din Rail Terminal Block Systems](#)

TE Part # **2271556-4**

TE Internal #: **2271556-4**

Terminal Block Type : **Spring Terminal Block**

Block Type : **Standard**

Connector System : **Cable-to-Cable**

Number of Positions : **1**

Centerline (Pitch) : **5.15 mm [ .202 in ]**


[Add to List](#) ▾

[Similar Products](#)



**ORDER SAMPLES**

**Compatible Parts & Tooling**



## SHOP OUR DISTRIBUTORS

North America ▾

Request pricing, availability and customization options

**CONTACT US**



## We are here to help!

Get in touch with our product experts.



**CHAT WITH US**



**EMAIL US**



**CALL US**

### DOCUMENTS

### FEATURES

### PRODUCT COMPLIANCE

#### Product Drawings

2.5MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK

[2.5MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK](#)

English

#### CAD Files

3D PDF

[3D\\_CVM\\_CVM\\_2271556-4\\_A.pdf](#) 3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2271556-4\\_A.2d\\_dxf.zip](#)

English

[ENG\\_CVM\\_CVM\\_2271556-4\\_A.3d\\_igs.zip](#)

English

[ENG\\_CVM\\_CVM\\_2271556-4\\_A.3d\\_stp.zip](#)

English

#### Product Specifications

Application Specification

[ENG\\_SS\\_114-137138\\_A3.pdf](#) English

Product Specification

[ENG\\_SS\\_108-137138\\_A3.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



## Product Type Features

Terminal Block Type : **Spring Terminal Block**

Block Type : **Standard**

Connector System : **Cable-to-Cable**

Sealable : **No**

Product Type : **Terminal Block**

## Configuration Features

Number of Positions : **1**

Number of Circuits : **2**

Ground Function : **Without**

Fuse Function : **Without**

Switch Function : **Without**

Number of Contacts : **1**

## Electrical Characteristics

Current Rating (A): **20**

Voltage Rating (VAC): **600**

Continuous Current Rating (A):  
**20**

## Contact Features

Contact Base Material : **Copper**

Contact Configuration : **Quick Connect**

Contact Current Rating (Max) (A):  
**20**

Contact Plating Material : **Matte Tin**

## Mechanical Attachment

Connector Mounting Type :  
**DIN Rail**

## Housing Features

Centerline (Pitch) : **5.15 mm [ .202 in ]**

Housing Color : **Red**

Housing Material : **Nylon**

## Dimensions

Wire Size : **28 – 12 AWG [ .08 – 2.5 kcmil ]**

## Usage Conditions

Operating Temperature Range (°C):  
**-40 – 105**

Operation/Application Circuit Application : **Power**

## Industry Standards

UL Flammability Rating : **UL 94V-0**

Statement of Compliance

[Statement of Compliance pdf](#)

## Compatible Parts

[> Contact Product Support](#)

## Also in the Series | [Din Rail Terminal Block Systems](#)



[Terminal Block Hardware \(26\)](#)




[Terminal Block Marking \(4\)](#)



[Terminal Blocks \(158\)](#)

## Customers Also Bought



**TE Part #** 68085  
**DIE COPALUM IP**  
**69099 6**



**TE Part #** 52746  
**SPLICE, COPALUM**  
**PARA 6**



**TE Part #** 52791  
**SPLICE, COPALUM**  
**PARA 16-14**



**TE Part #** 52792  
**SPLICE, COPALUM**  
**PARA 12-10**

[About TE Connectivity](#)

[For Partners](#)

[Customer Support](#)

**CALL US**

**LIVE CHAT**

[United States](#)

[Our Company](#)

[Events](#)

[TE News Center](#)

[Careers](#)


[Investors](#)

[Corporate Responsibility](#)


[Terms and Conditions of Sale](#)

[Distributors](#)

[Suppliers](#)

 [Email or Call Us](#)

 [Find Authorized Distributors](#)

 [What's New on TE.com](#)

 [Product FAQs](#)

[Select Country & Language](#)

[United States \(EN\)](#)

[Germany \(DE\)](#)

[China \(中文\)](#)

[Japan \(日本語\)](#)

[Find Your Country/Region](#) ▼