



+ RELAYS, CONTACTORS & SWITCHES

DIP & SIP SWITCHES



✓ Active

TE CONNECTIVITY (TE)

DIP SW ASSY-BLK LP ACT-4POS

Alcoswitch | 7000

5-435470-5

TE Internal Number: 5-435470-5

EU RoHS Compliant

EU ELV Compliant

Product Type Switch

Contact Mating Area Plating Material Gold

Housing Color Black

Housing Material Polyester GF

Auto-Insertable No

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

SWITCH ASSY, DIP, TYPE C, 7000 SERIES, SPDT & DPDT

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Application Specification

Dual In-Line Package (DIP) Programming Switches (7000 And 7100 Series)

PDF

English

Product Specification

Switch, DIP, Premium 7000 Series

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

Dual In-Line Package (DIP) Programming Switches (7000 And 7100 Series)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Switch

Sealed No

Switch Type DIP

Actuator Style Lever (Top Actuated)

Configuration Features

Number of Switches 1

Configuration (Pole-Throw) Double Pole - Double Throw

Number of Positions 4

Electrical Characteristics

Voltage Rating (VDC) 50

Contact Features

Contact Mating Area Plating Material Gold
Auto-Insertable No
Contact Current Rating (A) 1.5
Contact Base Material Copper Alloy
Solder Tail Contact Plating Gold over Nickel
Contact Mating Area Plating Thickness (µin) 30

Termination Features

Termination Post Length 3.56 mm [.14 in]

Mechanical Attachment

Mounting Type Through Hole

Housing Features

Low Profile Yes
Housing Color Black
Housing Material Polyester GF
Centerline 2.54 mm [.1 in]

Dimensions

Height 9.14 mm [.36 in]
Length 12.2 mm [.48 in]

Usage Conditions

Operating Temperature Range (°C) -55 – 105

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Quantity 25
Packaging Method Tube

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
