

## 5-1634514 -0 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**5-1634514 -0**

Active

### BNC RF Connectors

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Connector
- ? Connector Type = ZDC/BNC
- ? Jack
- ? Terminate To Coaxial Cable
- ? Coaxial Cable Termination Type = Crimp

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [BNC STRAIGHT JACK CRIMP 75 OHM RG59B/U, 62A/U, 140/U...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Connector
- ? Connector Type = ZDC/BNC
- ? [Gender](#) = Jack
- ? [Crimp Type](#) = Hex
- ? [Body Style](#) = Straight
- ? [Grade](#) = Commercial
- ? Body Shape = Round
- ? [Body Material](#) = Zinc
- ? [Sealed](#) = No
- ? [Isolated](#) = No
- ? [Dielectric Material](#) = Polymethylpentene
- ? Number of Ports = 1

#### Mechanical Attachment:

- ? Surface Mountable = No
- ? Panel Attachment = Without

#### Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 75

#### Termination Related Features:

- ? [Coaxial Cable Termination Type](#) = Crimp

#### Body Related Features:

- ? [Hardware Included](#) = No
- ? [Body Plating](#) = Nickel
- ? [Polarized](#) = No

#### Contact Related Features:

- ? [Center Contact Material](#) = Phosphor Bronze
- ? [Center Contact Plating](#) = Gold

#### Configuration Related Features:

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 140, 210, 59B, 62A, KX 25, KX 52, KX 53, KX 6A, URM 90

#### Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? [Terminate To](#) = Coaxial Cable

#### Packaging Related Features:

- ? Packaging Method = Tray
- ? Packaging Quantity = 100

#### Other:

- ? Brand = Tyco Electronics