


## 521383-3 Product Details

[Share](#) [Print](#) [Email](#)



521383-3

TE Internal Number: 521383-3

Active

[View 3D PDF](#)

### Positive Lock Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Connector
- Preloaded
- Connector Style = Header - Tab
- Contact Type = Tab
- Mating Area Interface Dimensions = 6.35 mm

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [ASSEMBLY, DIN, RAST 5, HEADER, VERTICAL \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version D\)](#)
- [3D Model \(IGES, Version D\)](#)
- [3D Model \(STEP, Version D\)](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector
- [Mount Angle](#) = Vertical
- [Color](#) = Black
- [Finish](#) = Tin
- [Keyed](#) = Yes
- [Polarization](#) = With

#### Dimensions:

- [Mating Area Interface Dimensions \(mm \[in\]\)](#) = 6.35 [.250]
- [PCB Thickness, Recommended \(mm \[in\]\)](#) = 1.50 [0.059]

#### Body Features:

- [Material](#) = Nylon 66
- [Position Keyed](#) = 1C, 2D
- [Polarized](#) = Yes
- [RAST Version](#) = 03-A
- [Latch Location-Centered Between Position](#) = 1 and 2

#### Contact Features:

- [Contact Type](#) = Tab

#### Housing Features:

- [Connector Style](#) = Header - Tab
- [Centerline \(mm \[in\]\)](#) = 5.00 [0.197]

#### Configuration Features:

- [Preloaded](#) = Yes
- [Number of Positions](#) = 3
- [Polarized Position\(s\)](#) = 1B

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- [UL Flammability Rating](#) = UL 94V-0

#### Conditions for Usage:

- [Applies To](#) = Printed Circuit Board

#### Packaging Features:

- [Packaging Method](#) = Bag, Box
- [Packaging Quantity](#) = 144

#### Other:

- [Line](#) = AMP DIN RAST 5
- [Brand](#) = TE Connectivity

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [AODA Accessibility Policy](#)
- [AODA Multi-Year Accessibility Plan](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed

