



554171-1 Product Details

[Share](#) [Print](#) [Email](#)



554171-1

TE Internal Number: 554171-1

Active

[View 3D PDF](#)

Cable Mounted Jacks

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector - Modular
- Region = Asia, Latin America, North America
- Jack Type = RJ11 / RJ14 / RJ25
- Performance Category = Cat 3
- Not Shielded

[View all Features](#)

Quick Links

- [▶ Pricing & Availability](#)
- [▶ Search for Tooling](#)
- [▶ Product Feature Selector](#)
- [▶ Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [keystone jack kit 6 position commercial \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Modular Jack, Kit Assembly, Keystone, 6 Position \(PDF, English\)](#)
- [Modular Jack, Kit Assembly, Keystone, 6 Position \(PDF, Japanese\)](#)

Application Specifications:

- None Available

Instruction Sheets:

- [Terminating Instruction for 6- and 8-Position Commer... \(PDF, English\)](#)

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version G\)](#)
- [3D Model \(IGES, Version G\)](#)
- [3D Model \(STEP, Version G\)](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector - Modular
- Jack Type = RJ11 / RJ14 / RJ25
- Performance Category = Cat 3
- Termination Style = Toolless
- Series = Keystone
- Wiring Pattern = One-to-one
- Keyed = No
- Stuffer Cap Type = Multiple
- Label Material = Adhesive Backed Polyester
- Stuffer Cap Material = Polycarbonate
- Stuffer Cap Color = Clear

Electrical Characteristics:

- Shielded = No

Termination Features:

- Solder Tail Contact Plating = Selective Tin

Dimensions:

- Conductor Outer Diameter (mm [in]) = 1.22 [0.048]

Body Features:

- NETCONNECT Select System = No
- Wire Range (mm [AWG]) = 0.12-0.40² [26-22]
- Mount Type = Panel Mount

Contact Features:

- Contact Base Material = Copper Alloy
- Contact Plating, Mating Area, Material = Gold

Housing Features:

- Housing Color = Black
- Housing Material = Polyphenylene Oxide
- UL Flammability Rating = UL 94V-0

Configuration Features:

- Dust Cover = Without
- Number of Positions = 6

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Converted to comply with RoHS directive

Packaging Features:

- Packaging Method = Individual
- Packaging Quantity = 25

Product Availability:

- Region = Asia, Latin America, North America

Other:

- Brand = TE Connectivity

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

