

 [Live Product Chat](#)



✓ Active

 [Add to Part List](#)

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Number of Positions = 15
- Receptacle
- PCB Mount Angle = Vertical
- Product Series = HDP-20
- Without Mating Connector Lock

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Mating Products \(7\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings:

- [15 pol hd-20 stiftstecker mit pfofen 0,63 x 0,63](#) (PDF, English)

- None Available

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- [PC Board Mount Specifications](#)

- Tooling
- Mating Products (7)

List all Documents

Product Type Features: • Number of Positions = 15 • Gender = Receptacle • PCB Mount Angle = Vertical • Product Series = HDP-20 • Mating Connector Lock = Without • PCB Retention Feature = No • Shell Type = Full Metal • Shell Size = 2 • PCB Thickness (in [mm]) = 0.062 [1.57] • Grounding Indents = Without • Grounding Straps = Without • PCB Mount Style = Thru Hole • Color Code = None • Sealed = No • Post Size (mm [in]) = 0.64 [.025] • Shell Material = Steel • Comment = All Assemblies are pre-loaded with size 20 posted contacts. 1.2 mm pc board holes are recommended.	Body Related Features: • Insert Flammability Rating = UL 94V-0 • Insert Material = Brass • Shell Plating = Tin
Mechanical Attachment: • Panel Attachment = Without	Contact Related Features: • Contact Mating Area Plating Material = Gold (30) • Contact Shape = Square • Contact Material = Phosphor Bronze
Termination Related Features: • Grounding Clips = Without • Termination (Solder) Post Length (mm [in]) = 3.20 [0.126] • Solder Tail Contact Plating = Tin	Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C • RoHS/ELV Compliance History = Always was RoHS compliant
	Operation/Application: • Application = Standard
	Other: • Brand = AMP