

# 62305-3 Product Details

[Share](#) | [Print](#) | [Email](#)


## Splices - Open Barrel

AMVAR SPLC 600-3000 016TPBR

**62305-3**

TE Internal Number: 62305-3

**Active**

[View 3D PDF](#)

**Product Highlights** [View All](#)

- Splice
- Non-Insulation Support
- Wire/Cable Type = Magnet Wire
- Wire/Cable Size = 600 - 3,000 CMA
- With Serrations

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Splice
Insulation Support	Non-Insulation Support
Wire/Cable Type	Magnet Wire
Serrations	With Serrations
Number of Serrations	9
Splicing Type	Pigtail
Finish	Tin
Termination Features	
Wire/Cable Size (CMA)	600 - 3,000
Crimp Width (mm [in])	2.79 [0.110]
Body Features	
Stock Thickness (mm [in])	0.41 [0.016]
Material	Phosphor Bronze

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant
Packaging Features	
Packaging Method	Reel
Packaging Quantity	30,000
Other	
Brand	AMP
Proprietary Name	AMPLIVAR
Node Classification	Splices

**Related Products**

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

**Corporate Information**

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

**Quick Links**

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

**Customer Support**

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

**Keep Me Informed**