


638187 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



638187 -1

[Active](#)

Miscellaneous Automotive

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? [Contact](#)
- ? [Contact Type = Receptacle](#)
- ? [Mount = Wire Crimp](#)
- ? [Wire Range = 0.50 -0.90² \[20-18\] mm \[AWG\]](#)
- ? [Pre-Tin \(Bright\) Contact Mating Area Plating Material](#)

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [RECEPTACLE CONTACT, DUAL BEAM](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [Category 1 Automotive Plug Connector Assemblies](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Contact
- ? [Mount](#) = Wire Crimp

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 0.50 -0.90² [20-18]

Contact Related Features:

- ? [Contact Type](#) = Receptacle
- ? [Contact Mating Area Plating Material](#) = Pre -Tin (Bright)
- ? [Contact Material](#) = Copper Alloy

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- ? [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Packaging Related Features:

- ? [Packaging Method](#) = Reel

Other:

- ? [Brand](#) = AMP