

638551 -3 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



638551 -3

[Active](#)

Miscellaneous Automotive

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Contact
- ? Contact Type = Receptacle
- ? Mount = Wire Crimp
- ? Wire Range = 0.50 -0.90² [20-18] mm [AWG]
- ? Pre-Tin Contact Mating Area Plating Material

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:
? [CONTACT, FEMALE, .64mm TIN PLATED](#) (PDF, English)

Catalog Pages/Data Sheets:
? None Available

Product Specifications:
? [0.64 mm USCAR Contact System](#) (PDF, English)

Application Specifications:
? [0.64 mm Contact System](#) (PDF, English)

Instruction Sheets:
? [0.64 mm Automotive Sealed Plug Connectors](#) (PDF, English)
? [0.64mm Unsealed Dual -Row Automotive Plug Connectors ...](#) (PDF, English)

CAD Files:
? None Available

[List all Documents](#)

Additional Information:
? [Product Line Information](#)

Related Products:
? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
? [Product Type](#) = Contact
? Mount = Wire Crimp
? Comment = See customer drawing for reeling direction.

Body Related Features:
? [Wire Range \(mm \[AWG\]\)](#) = 0.50 -0.90² [20-18]

Contact Related Features:
? [Contact Type](#) = Receptacle
? [Contact Mating Area Plating Material](#) = Pre -Tin
? Contact Material = Brass

Industry Standards:
? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
? [Lead Free Solder Processes](#) = Not relevant for lead free process
? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:
? Packaging Method = Reverse Reeled

Other:
? Brand = AMP