

750877-7 Product Details

[Live Product Chat](#)



750877-7

TE Part Number: 750877-7

[Active](#)

[Add to Part List](#)

.050 Series Cable Connectors (SCSI)

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Hardware
- Hardware Type = Wire Lacing Cover
- Number of Positions = 68
- Wire/Cable Type = Round Jacketed Cable
- Wire Range = 0.05-0.09² [30-28] mm [AWG]

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [COVER, TERMINATING, DISCRETE WIRE, AMPLIMITE](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Connector, AMPLIMITE, Shielded, .050 Series](#) (PDF, English)

Application Specifications:

- [AMPLIMITE .050 Series Insulation Displacement and Pr...](#) (PDF, English)

Instruction Sheets:

- [Manual Arbor Frame Assembly 58024-1](#) (PDF, English)
- [AMP* REPAIR TOOL 58430-1 FOR AMPLIMITE* .050-SERIES ...](#) (PDF, English)
- [AMPLIMITE .050 Series Connectors \(Round-to-Flat Cable\)](#) (PDF, English)
- [Installation and Use of Mass Termination Tooling](#) (PDF, English)
- [Cover Lacing Fixture 91293-1 for AMPLIMITE .050 Seri...](#) (PDF, English)
- [AMP* MANUAL MINIATURE APPLICATOR FRAME ASSEMBLY 91295-1](#) (PDF, English)
- [Cover Closing Kits and Staple Inserter Kit](#) (PDF, English)
- [Tooling Kit 768900-1](#) (PDF, English)

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Hardware
- Number of Positions = 68
- [Wire/Cable Type](#) = Round Jacketed Cable
- [Wire Insulation Diameter \(mm \[in\]\)](#) = 0.74 - 0.91 [0.029 - 0.036]
- [Mating Connector Lock](#) = Without
- [Product Series](#) = Series III
- Color = Black

Mechanical Attachment:

- Hardware Type = Wire Lacing Cover

Body Related Features:

- Wire Range (mm [AWG]) = 0.05-0.09² [30-28]

Housing Related Features:

- Housing Material = Thermoplastic
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Terminate To = Wire

Other:

- Brand = AMP