

828085-2 Product Details

[Live Product Chat](#)



828085-2

TE Part Number: 828085-2

[Active](#)

[Add to Part List](#)

CPC Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Number of Positions = 37
- Receptacle
- For Use With Socket Contacts
- Not Preloaded

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

Documentation & Additional Information

Product Drawings:

- [37 pol steckteil mit metallkupplungsring](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Contact Arrangement](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Number of Positions](#) = 37
- [Gender](#) = Receptacle
- For Use With = Socket Contacts
- Termination Style = Wire
- [Shell Size](#) = 23
- [Shell Type](#) = All Plastic
- [Product Series](#) = Series 1
- [Thread Size](#) = 1-3/8 - 18 UNEF-2A
- [Sealed](#) = No

Mechanical Attachment:

- [Preloaded](#) = No
- [VDE Tested](#) = No

Body Related Features:

- [Mount Style](#) = Free Hanging
- Coupling Ring Material = Aluminum

Contact Related Features:

- [Standard or Reverse Gender](#) = Reverse
- Coupling Ring Diameter (mm [in]) = 46.00 [1.182]

Housing Related Features:

- Housing Material = PA 6.6
- Housing Color = Black
- Housing Flammability Rating = UL 94V-0

Configuration Related Features:

- [Reverse Numbering](#) = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = AMP