



# SFP/SFP+/ZSFP+



## TE CONNECTIVITY (TE) DWDM Kit Assy, PCI (4.2) SFP | DWDM

1367645-4  
TE Internal Number: 1367645-4

Always EU RoHS/ELV Compliant

Form Factor **SFP**

Product Type **Cage Assembly**

Data Rate (Max) (Gb/s) **4**

EMI Containment **External Springs**

Cage Type **Single**

✓ Active

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

### Product Drawings

[KIT ASSEMBLY, PRESS FIT, DWDM SFP](#)  
PDF  
**English**

### CAD Files

[3D PDF](#)  
PDF  
**3D**

[Customer View Model](#)  
2D\_DXF.ZIP  
**English**

[Customer View Model](#)  
3D\_IGS.ZIP  
**English**

[Customer View Model](#)  
3D\_STP.ZIP  
**English**

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Form Factor	<b>SFP</b>
	Product Type	<b>Cage Assembly</b>
	Included Heat Sink	<b>Yes</b>
	Included Lightpipe	<b>No</b>

### Configuration Features

	EMI Containment	<b>External Springs</b>
	Port Configuration	<b>1x1</b>
	Number of Ports	<b>1</b>
Signal Characteristics	Data Rate (Max) (Gb/s)	<b>4</b>
Body Features	Heat Sink Style	<b>Pin</b>
	Heat Sink Height	<b>4.2 mm [ .165 in ]</b>
Termination Features	Termination Method to PC Board	<b>Through Hole - Press-Fit</b>
Mechanical Attachment	PCB Mounting Style	<b>Double-Sided (Belly-to-Belly)</b>
Housing Features	Cage Type	<b>Single</b>
	Cage Material	<b>Copper Alloy</b>
Dimensions	PCB Thickness (Recommended)	<b>2.25 mm [ .089 in ]</b>
	Tail Length	<b>3 mm [ .118 in ]</b>
Operation/Application	Heat Sink Compatible	<b>Yes</b>
	For Use With	<b>SFP SMT Connector</b>
Packaging Features	Packaging Method	<b>Tray/Box</b>
Product Compliance	<a href="#">Statement of Compliance</a> PDF  <a href="#">VIEW ALL PRODUCT COMPLIANCE</a>	