



Active

PRODUCT DRAWING
English

[See All Documentation](#)

TE CONNECTIVITY

DWDM Kit Assy, Networking (1367645-6)

SFP | DWDM

1367645-6

TE Internal Number: 1367645-6

Always EU RoHS/ELV Compliant

Product Type **Cage Assembly**

Included Lightpipe **No**

EMI Containment **External Springs**

PCB Mounting Style **Double-Sided (Belly-to-Belly)**

Form Factor **SFP**

[See All Features](#)

North America

DISTRIBUTOR	QUANTITY	DATE AS OF
MASTER ELECTRONICS CORP. 1-888-473-5297	60	2015/09/04
ONLINE COMPONENTS 1-888-473-5297	20	2015/09/03

- [GET SAMPLE](#)
- [SAVE TO LIST](#)
- [CHECK FOR TOOLING](#)
- [FIND SIMILAR PRODUCTS](#)

DOCUMENTATION FEATURES

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Product Type	Cage Assembly
	Included Lightpipe	No
	Form Factor	SFP
	Included Heat Sink	Yes
	Applies To	Printed Circuit Board
	Product Line	SFP
Configuration Features	EMI Containment	External Springs
	Number of Ports	1
	Port Configuration	1x1
Body Features	Heat Sink Style	Pin
	Heat Sink Height	13.5mm[.531in]
Termination Features	Termination Method to PC Board	Through Hole - Press-Fit
Mechanical Attachment	PCB Mounting Style	Double-Sided (Belly-to-Belly)
Housing Features	Cage Type	Single
	Cage Material	Copper Alloy
	Cage Plating Material	Tin over Nickel Flash
Dimensions	PCB Thickness (Recommended)	2.25mm[.089in]
	Tail Length	3mm[.118in]
Operation/Application	Heat Sink Application	Yes
	Heat Sink Compatible	Yes
	For Use With	SFP SMT Connector
Packaging Features	Packaging Method	Tray/Box
Product Compliance	Statement of Compliance PDF VIEW ALL PRODUCT COMPLIANCE	

COMPATIBLE

No compatible products found for 1367645-6