



178093-1



✓ Active

TE CONNECTIVITY (TE)

040/070 HYBRID CAP ASSY 38P

178093-1

TE Internal Number: 178093-1

EU RoHS Compliant

EU ELV Compliant

↓ **PRODUCT DRAWING**
Japanese

↓ **3D PDF**

DOCUMENTATION

Product Drawings

38Pos.CAP HOUSING ASS'Y .040/.070 HYBRID I/O CONN.(NON FLANGE TYPE)

PDF

Japanese

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

.040/.070 Hybrid I/O Conn. For Printed Circuit Board

PDF

Japanese

040II/070II Hybrid I/O Connector MK-II For Wire-TO-Board Termination

PDF

Japanese

.040II/.070II Hybrid I/O Connector MK-II For Wire-To-Board Termination

PDF

Japanese

Application Specification

MULTILOCK 040/070 And 070/250 Series Hybrid Connectors

PDF

English

Instruction Sheets

Customer Manual (non U.S.)

.040/.070 HYBRID I/O MK-II CONNECTOR

PDF

Japanese

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Detailed product features are not currently available online.

Statement of Compliance

Statement of Compliance

PDF