



CONNECTORS

AUTOMOTIVE CONNECTOR CAPS & COVERS



✓ Active

TE CONNECTIVITY (TE)

WIRE COVER FOR EUI 37P PLUG

1897266-2

TE Internal Number: 1897266-2

EU RoHS Compliant

EU ELV Compliant

Connector System Wire-to-Component

Accessory Type Wire Cover

Cable Exit Angle 90

Sealable Yes

Strain Relief Without

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

WIRE COVER

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Component

Accessory Type Wire Cover

Sealable Yes

Strain Relief Without

Body Features

Cable Exit Angle 90

Color Black

Material PA

Dimensions

Cable Bundle Diameter 19 mm [.748 in]

Usage Conditions

Operating Temperature Range -40 – 125 °C [-40 – 248 °F]

Operating Temperature (Max) (°C) 70, 75, 80, 85, 90, 100, 105, 110, 120

Operating Temperature (Max) (°F) 158, 167, 176, 185, 194, 212, 221, 230, 248

Industry Standards

UL Flammability Rating UL 94V-2

Packaging Features

Packaging Method Box

Packaging Quantity 120

Other

Serviceable Yes

Statement of Compliance

Statement of Compliance

PDF

