



TE CONNECTIVITY (TE)

250 SERIES P/L EX-II REC HSG 2P SHUROUD

Positive Lock | 250

1939581-1

TE Internal Number: 1939581-1

Always EU RoHS/ELV Compliant

Centerline **15 mm [.59 in]**

Number of Positions **2**

Number of Rows **1**

Mating Retention **Without**

✓ Active

↓ **PRODUCT DRAWING**
Japanese

↓ **3D PDF**

Product Drawings

[250 SERIES POSITIVE LOCK EX-II REC HSG SHROUD TYPE 15MM PITCH 2POS](#)

PDF (TIFF AVAILABLE)

Japanese

[250 SERIES POSITIVE LOCK EX-II REC HSG SHROUD TYPE 15MM PITCH 2POS](#)

PDF (TIFF AVAILABLE)

Japanese

CAD Files

[3D PDF](#)

PDF

3D

[Customer View Model](#)

2D_DXF.ZIP

English

[Customer View Model](#)

3D_IGS.ZIP

English

[Customer View Model](#)

3D_STP.ZIP

English

Product Specifications

Product Specification

[250 SERIES POSITIVE LOCK EX-II CONNECTOR](#)

TIF

Japanese

[250 SERIES POSITIVE LOCK EX-II CONNECTOR](#)

PDF

Japanese

Product Type Features	Glow Wire Rating	Standard Part - Not Glow Wire
	Sealed	No
	Connector Type	Housing
	Applies To	Wire/Cable
	Connector Style	Receptacle
	Connector System	Wire-to-Wire
	Product Type	Connector

Configuration Features	Number of Positions	2
	Number of Rows	1
	Number of Columns	2
	Preloaded	No

Electrical Characteristics	Operating Voltage	250 VAC
----------------------------	-------------------	----------------

Contact Features	Contact Type	Socket
	Contact Layout	Inline
	Accepts Contact Type	Tab

Mechanical Attachment	Mating Retention	Without
	Mating Connector Lock	Without
	Mating Alignment	With
	Mating Alignment Type	Polarization

Housing Features	Centerline	15 mm [.59 in]
	Housing Color	Natural
	Housing Style	Receptacle
	Housing Material	Nylon

Dimensions	Height	8.6 mm [.338 in]
	Length	23.8 mm [.937 in]
	Width	24.4 mm

Usage Conditions	Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
------------------	-----------------------------	--------------------------------------

Operation/Application	For Use With	Plug Housing
Industry Standards	UL Flammability Rating	UL 94V-0
Packaging Features	Packaging Quantity	200
	Packaging Method	Bag
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	