



+ CABLE ASSEMBLIES

PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE) CA MINI IO MINI IO TYPE I

2-2205131-3
 TE Internal Number: 2-2205131-3

Always EU RoHS/ELV Compliant

Cable Assembly Type **Mini I/O**

Equalized **No**

Wire Size (AWG) **26**

Wire Size (mm²) **.129**

Overall Outside Cable Diameter **.244 in, 6.2 mm**

Product Drawings

CA MINI IO MINI IO TYPE I

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Cable Assembly Type	Mini I/O
	Shielded	Yes
	Connector Type (End A)	RJ45 Plug
	Connector Type (End B)	RJ45 Plug
	Product Type	Cable Assembly
	Cable Assembly Category	Industry Standard
	Product Designation	Patch Cord
	Performance Category	Category 5E Performance for 10/100/1000BASE-T
	Latching Style	Slide Latch
	Twisted Pairs	Yes

Configuration Features	Number of Positions	8
	Number of Signal Positions	8
	Configuration	Double-Ended



Electrical Characteristics	Impedance (Ω)	100
Signal Characteristics	Data Rate (Gb/s)	1
Body Features	Equalized	No
	Color	Black
	Shield Material	Copper Alloy
	Jacket Material	PUR
Contact Features	Contact Mating Area Plating Material	Gold
	Contact Mating Area Plating Thickness	.5 μm, 19.68 μin
Mechanical Attachment	Jackscrew	Without
Housing Features	Housing Material	Thermoplastic
Dimensions	Wire Size (AWG)	26
	Wire Size (mm ²)	.129
	Overall Outside Cable Diameter	.244 in, 6.2 mm
	Cable Assembly Length	2 m [6.56 ft]
Operation/Application	Halogen Free	Yes
Industry Standards	Flammability Rating	UL 444
	IEEE 1394	No
Other	CLOUDSPLITTER	No
Product Compliance	Statement of Compliance PDF VIEW ALL PRODUCT COMPLIANCE	