



STANDARD CIRCULAR CONNECTORS



✓ Active

[↓ PRODUCT DRAWING](#)
English

TE CONNECTIVITY (TE)
M12.MALE.A CODE.R/A.4P.PG9.(AU)
[AMP](#) | [M12](#)

2-2271122-2
 TE Internal Number: 2-2271122-2

Always EU RoHS/ELV Compliant

Product Type **Connector**

Wire/Cable Size (AWG) **18**

Shielded **No**

Number of Positions **3**

Contact Layout **Circular**

Product Drawings

[M12 MALE 90 DEG ANGLED FIELD INSTALLABLE, UNSHIELDED CONNECTOR,](#)
 PDF
English

Catalog Pages/Data Sheets

[M8 / M12 Connector System Catalog](#)
 PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Product Type	Connector
	Shielded	No
Configuration Features	Number of Positions	3
	Keying	A
Electrical Characteristics	Operating Voltage (VAC)	250
Body Features	Feedthrough Type	Yes
Contact Features	Contact Layout	Circular
	Contact Type	Pin

Housing Features	Alignment Keyed	45°
------------------	-----------------	------------

Dimensions	Wire/Cable Size (AWG)	18
------------	-----------------------	-----------

Usage Conditions	Operating Temperature Range (°C)	-40 – 85
------------------	----------------------------------	-----------------

Packaging Features	Packaging Quantity	1
--------------------	--------------------	----------

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)