



PLUGGABLE I/O CABLE ASSEMBLIES



TE CONNECTIVITY (TE) CA 200MM 06 POS. MOW-MOW M-M VALUE LINE

2205104-3
 TE Internal Number: 2205104-3

[Always EU RoHS/ELV Compliant](#)

Cable Assembly Type **MOW to MOW**

Equalized **No**

Wire Size (AWG) **28**

Cable Assembly Length **.2 m [.656 ft]**

Color **Gray**

✓ Active

[↓ PRODUCT DRAWING](#)
 English

Product Drawings

[CABLE ASSY MICRO-MATCH MOW-MOW VALUE-LINE](#)
 PDF
 English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Cable Assembly Type	MOW to MOW
	Product Type	Cable Assembly
	Cable Assembly Category	Industry Standard
	Product Designation	Patch Cord
Configuration Features	Number of Power Positions	6
	Keyed	No
	Configuration	Double-Ended
Body Features	Equalized	No
	Color	Gray
Dimensions	Wire Size (AWG)	28
	Cable Assembly Length	.2 m [.656 ft]

Industry Standards

Flammability Rating

UL 2651

IEEE 1394

No

Other

CLOUDSPLITTER

No

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)