



PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE) CA 200MM 08 POS. MOW-MOW M-M VALUE LINE

2205105-3
TE Internal Number: 2205105-3

- Always EU RoHS/ELV Compliant
- Cable Assembly Type **MOW to MOW**
- Equalized **No**
- Wire Size (AWG) **28**
- Cable Assembly Length **.2 m [.656 ft]**
- Color **Gray**



Product Drawings

[CABLE ASSY MICRO-MATCH MOW-MOW VALUE-LINE](#)
PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Assembly Type	MOW to MOW
Product Type	Cable Assembly
Cable Assembly Category	Industry Standard
Product Designation	Patch Cord

Configuration Features

Number of Power Positions	8
---------------------------	----------

Keyed	No
Configuration	Double-Ended

Body Features	Equalized	No
	Color	Gray

Dimensions	Wire Size (AWG)	28
	Cable Assembly Length	.2 m [.656 ft]

Industry Standards	Flammability Rating	UL 2651
	IEEE 1394	No

Other	CLOUDSPLITTER	No
-------	---------------	-----------

Product Compliance	Statement of Compliance
	PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

