



PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

[↓ PRODUCT DRAWING](#)
English

TE CONNECTIVITY (TE)

CA 75MM 10 POS. MOW-PB M-M VALUE LINE

2205115-1

TE Internal Number: 2205115-1

Always EU RoHS/ELV Compliant

Cable Assembly Type **MOW to PB**

Equalized **No**

Wire Size (AWG) **28**

Cable Assembly Length **.075 m [.246 ft]**

Color **Gray**

Product Drawings

CABLE ASSY MICRO-MATCH MOW-PB VALUE-LINE

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Cable Assembly Type	MOW to PB
	Product Type	Cable Assembly
	Cable Assembly Category	Industry Standard
	Product Designation	Patch Cord
Configuration Features	Number of Power Positions	10
	Keyed	No
	Configuration	Double-Ended
Body Features	Equalized	No
	Color	Gray
Dimensions	Wire Size (AWG)	28
	Cable Assembly Length	.075 m [.246 ft]

Industry Standards

Flammability Rating

UL 2651

IEEE 1394

No

Other

CLOUDSPLITTER

No

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)