



PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE)

CA 75MM 14 POS. MOW-PB M-M VALUE LINE

2205117-1

TE Internal Number: 2205117-1

Always EU RoHS/ELV Compliant

Cable Assembly Type **MOW to PB**

Equalized **No**

Wire Size (AWG) **28**

Cable Assembly Length **.075 m [.246 ft]**

Color **Gray**

Product Drawings

CABLE ASSY MICRO-MATCH MOW-PB VALUE-LINE

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

| | | |
|------------------------|---------------------------|---------------------------|
| Product Type Features | Cable Assembly Type | MOW to PB |
| | Product Type | Cable Assembly |
| | Cable Assembly Category | Industry Standard |
| | Product Designation | Patch Cord |
| Configuration Features | Number of Power Positions | 14 |
| | Keyed | No |
| | Configuration | Double-Ended |
| Body Features | Equalized | No |
| | Color | Gray |
| Dimensions | Wire Size (AWG) | 28 |
| | Cable Assembly Length | .075 m [.246 ft] |

Industry Standards

Flammability Rating

UL 2651

IEEE 1394

No

Other

CLOUDSPLITTER

No

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)