



## PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

↓ **PRODUCT DRAWING**  
English

### TE CONNECTIVITY (TE) CA 75MM 18 POS. MOW-PB M-M VALUE LINE

2205119-1  
TE Internal Number: 2205119-1

[Always EU RoHS/ELV Compliant](#)

Cable Assembly Type **MOW to PB**

Equalized **No**

Wire Size (AWG) **28**

Cable Assembly Length **.075 m [ .246 ft ]**

Color **Gray**

### Product Drawings

#### [CABLE ASSY MICRO-MATCH MOW-PB VALUE-LINE](#)

PDF  
**English**

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Cable Assembly Type	<b>MOW to PB</b>
	Product Type	<b>Cable Assembly</b>
	Cable Assembly Category	<b>Industry Standard</b>
	Product Designation	<b>Patch Cord</b>
Configuration Features	Number of Power Positions	<b>18</b>
	Keyed	<b>No</b>
	Configuration	<b>Double-Ended</b>
Body Features	Equalized	<b>No</b>
	Color	<b>Gray</b>
Dimensions	Wire Size (AWG)	<b>28</b>
	Cable Assembly Length	<b>.075 m [ .246 ft ]</b>

---

Industry Standards

Flammability Rating

**UL 2651**

IEEE 1394

**No**

---

Other

CLOUDSPLITTER

**No**

---

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)