




# HEADERS & RECEPTACLES



✓ Active

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

TE CONNECTIVITY (TE)

## 3P, PL RAST 5 Tab Header, TH, Vertical

[RAST](#) | [RAST 5D](#)

2232532-3

TE Internal Number: 2232532-3

Always EU RoHS/ELV Compliant

Centerline **5 mm [ .197 in ]**

Number of Positions **3**

PCB Mounting Orientation **Vertical**

Color **Natural**

### Product Drawings

[ASSEMBLY, POSITIVE LOCK RAST 5, HEADER VERTICAL](#)

PDF  
**English**

### CAD Files

[3D PDF](#)

PDF  
**3D**

[Customer View Model](#)

2D\_DXF.ZIP  
**English**

[Customer View Model](#)

3D\_IGS.ZIP  
**English**

[Customer View Model](#)

3D\_STP.ZIP  
**English**

### Product Specifications

Product Specification

[Design Objective Of RAST 5 Tab Headers](#)

PDF  
**English**

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

PCB Mounting Orientation

**Vertical**

Product Type

**Connector**

	Connector Type	<b>Header</b>
	Applies To	<b>Printed Circuit Board</b>
Configuration Features	Number of Positions	<b>3</b>
	Preloaded	<b>Yes</b>
	Position Keyed	<b>1C,2D</b>
Body Features	Color	<b>Natural</b>
	Plating Material	<b>Tin</b>
	Material	<b>Nylon</b>
Contact Features	Contact Type	<b>Tab</b>
Mechanical Attachment	Mating Area Interface Dimensions	<b>.25 in, 6.35 mm</b>
	Polarized Positions	<b>1B</b>
Housing Features	Centerline	<b>5 mm [ .197 in ]</b>
Dimensions	PCB Thickness (Recommended)	<b>1.5 mm [ .059 in ]</b>
Industry Standards	UL Flammability Rating	<b>UL 94V-0</b>
Product Compliance	<a href="#">Statement of Compliance</a> PDF  <a href="#">VIEW ALL PRODUCT COMPLIANCE</a>	