



+ CONNECTORS

AUTOMOTIVE CONNECTOR CAPS & COVERS



TE CONNECTIVITY (TE)

COVER FOR 94 POS. RECEPTACLE HOUSING

284722-1

TE Internal Number: 284722-1

Always EU RoHS/ELV Compliant

Accessory Type **Cover**

Cable Exit Angle **180°**

Strain Relief **With**

Color **Black**

Material **PA GF**

✓ Active

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

Product Drawings

COVER FOR 94 POS. RECEPTACLE HOUSING

PDF **(TIFF AVAILABLE)**
English

COVER FOR 94 POS. RECEPTACLE HOUSING

PDF **(TIFF AVAILABLE)**
English

CAD Files

3D PDF

PDF
3D

Customer View Model

2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP
English

Customer View Model

3D_STP.ZIP
English



Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Accessory Type **Cover**

Strain Relief **With**

Connector System **Wire-to-Board**

Sealed **No**

Configuration Features	Number of Positions	94
Body Features	Cable Exit Angle	180°
	Color	Black
	Material	PA GF
Usage Conditions	Operating Temperature (Max) (°C)	70, 75, 80, 85, 90, 100, 105, 110, 120, 125
	Operating Temperature (Max) (°F)	158, 167, 176, 185, 194, 212, 221, 230, 248, 257
	Operating Temperature Range	-40 – 125 °C [-40 – 257 °F]
Industry Standards	UL Flammability Rating	None
Packaging Features	Packaging Quantity	350
	Packaging Method	Box
Other	Serviceable	Yes
Product Compliance	<p>Statement of Compliance PDF</p> <p>VIEW ALL PRODUCT COMPLIANCE</p>	