




# RECTANGULAR POWER CONNECTORS



✓ Active

## TE CONNECTIVITY (TE) POWER DBL LOCK CAP HSG F/H 3P(GWT)

[Power-Signal Double Lock](#) | [Power Double Lock](#)

5-179464-1  
 TE Internal Number: 5-179464-1

Always EU RoHS/ELV Compliant

Product Type **Housing**

Housing Type **Receptacle**

Connector System **Wire-to-Wire**

Applies To **Wire/Cable**

Number of Positions **3**

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Product Type	<b>Housing</b>
	Housing Type	<b>Receptacle</b>
	Contact Type	<b>Tab</b>
Configuration Features	Number of Positions	<b>3</b>
	Centerline	<b>3.96 mm [ .156 in ]</b>
	Number of Rows	<b>1</b>
	Multiple Contact Types	<b>Without</b>
Electrical Characteristics	Operating Voltage (VAC)	<b>300</b>
Contact Features	Contact Retention	<b>Without</b>
Mechanical Attachment	Assembly Integration Feature	<b>Without</b>
Housing Features	Housing Color	<b>Natural</b>
	Housing Material	<b>Nylon 6/6</b>

Dimensions	Width (mm)	<b>9.4</b>
	Height	<b>26.1 mm [ 1.02 in ]</b>
	Length (mm)	<b>13.9</b>
<hr/>		
Usage Conditions	Sealed Condition	<b>Not Sealed</b>
<hr/>		
Operation/Application	Connector System	<b>Wire-to-Wire</b>
	Applies To	<b>Wire/Cable</b>
	Operating Temperature	<b>-30 – 105 °C [ -22 – 221 °F ]</b>
<hr/>		
Identification Marking	Circuit Identification Feature	<b>Without</b>
<hr/>		
Industry Standards	CSA Rating	<b>Certified</b>
	CSA File Number	<b>LR7189</b>
	Agency/Standard	<b>CSA, UL</b>
<hr/>		
Packaging Features	Packaging Method	<b>Bag</b>
	Packaging Quantity	<b>200</b>
<hr/>		
Other	Selectively Loaded	<b>No</b>
<hr/>		
Product Compliance	<a href="#">Statement of Compliance</a> PDF	
	<a href="#">VIEW ALL PRODUCT COMPLIANCE</a>	