




CONNECTOR HOUSINGS



TE CONNECTIVITY (TE) POWER D/LOCK PLUG HG 4P NAT(GWT)

Power-Signal Double Lock | Power Double Lock

5-316501-1
 TE Internal Number: 5-316501-1

Always EU RoHS/ELV Compliant

Connector System **Wire-to-Wire**

Centerline **3.96 mm [.156 in]**

Number of Positions **4**

Number of Rows **1**

Housing Material **Nylon 6/6**

✓ Active

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Connector System	Wire-to-Wire
	Connector Style	Plug
	Sealed	No
	Applies To	Wire/Cable
	Product Type	Connector
	Connector Type	Housing

Configuration Features	Number of Positions	4
	Number of Rows	1
	Selectively Loaded	No
	Preloaded	No

Electrical Characteristics	Operating Voltage (VAC)	300
----------------------------	-------------------------	------------

Body Features	Sealable	No
---------------	----------	-----------

Contact Features	Contact Type	Socket
------------------	--------------	---------------

	Shunts/Shorting Bars	Without
	Multiple Contact Types	Without
Mechanical Attachment	Contact Retention	Without
Housing Features	Centerline	3.96 mm [.156 in]
	Housing Material	Nylon 6/6
	Housing Color	Natural
Dimensions	Height	20.6 mm [.811 in]
Usage Conditions	Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
Operation/Application	Assembly Integration Feature	Without
Identification Marking	Circuit Identification Feature	Without
Industry Standards	CSA Rating	Certified
	CSA File Number	LR7189
	UL Rating	Recognized
	CSA Certified	Yes
	VDE Tested	Yes
	Agency/Standard	CSA, UL
	UL File Number	E28476
Packaging Features	Packaging Quantity	250
	Packaging Method	Bag
Product Compliance	Statement of Compliance PDF VIEW ALL PRODUCT COMPLIANCE	