

 [Live Product Chat](#)



TE Part Number: 2-1437406-9

Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Number of Circuits = 18
- 9.53 mm Centerline
- Bright Tin Contact Mating Area Plating Material
- Without Card Guides
- PSB Series

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings:

- [TERMINAL BLOCK 90 DEGREE PSB \(.375 SPACING\)](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Number of Circuits = 18
- Screw Material = Steel
- Comment = Do not order terminal screw and clamp in combination with any other top hardware.

Mechanical Attachment:

- Screw Plating = Zinc Chromate

Electrical Characteristics:

- Double Sided = No
- Terminal Screw Angle = 90°
- Terminal Screw Type = #6 Phil-slot steel screw and clamp
- Clamp Material = Brass
- Current Rating, Max. (Amps.) = 5 (Class D Limited Rating), 10 (Class C General Industrial)

Body Related Features:

- Centerline (mm [in]) = 9.53 [0.375]
- Card Guides = Without
- Series = PSB
- Clamp Plating = Zinc Chromate

Contact Related Features:

- Contact Mating Area Plating Material = Bright Tin

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Buchanan