

**1 - 1825096 - 4 Product Details**

[Live Product Chat](#)



**1 - 1825096 - 4**

TE Part Number: 1 - 1825096 - 4

[Active](#)

[Add to Part List](#)

**Pushbutton Switches**

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

**Product Highlights:**

- ? Switch - Mechanical
- ? Tactile
- ? Double Pole - Single Throw Configuration (Pole - Throw)
- ? Contact Rating = 0.4VA
- ? Operating Function = Off [On]

[View all Features](#) | [Find Similar Products](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [PUSHBUTTON SWITCH, TPA SERIES](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:** ( [CAD Format & Compression Information](#) )

- ? [2D Drawing](#) (DXF, Version A)
- ? [3D Model](#) (IGES, Version A)
- ? [3D Model](#) (STEP, Version A)

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? Product Type = Switch - Mechanical
- ? Tactile = Yes
- ? Configuration (Pole - Throw) = Double Pole - Single Throw
- ? Mount Angle = Right Angle
- ? Termination Type = Printed Circuit
- ? Actuator Style = Round

**Electrical Characteristics:**

- ? Contact Rating = 0.4VA

**Body Related Features:**

- ? [Series](#) = TPA
- ? Mount Style = Through -Hole
- ? Actuator Length (mm [in]) = 3.84 [0.151]
- ? Actuator Profile = Extended
- ? Actuator Color = Black
- ? Case Material = Thermoplastic (LCP)
- ? Actuator Material = Nylon

**Contact Related Features:**

- ? Contact Plating = Gold
- ? Contact Material = Copper Alloy

**Housing Related Features:**

- ? Process Sealed = No
- ? Low Profile = No

**Configuration Related Features:**

- ? Operating Function = Off [On]
- ? Ganged = No
- ? ESD Grounding Terminal = Without
- ? Actuator Force (g [oz]) = 50.00 - 400.00 [1.770 - 14.120]
- ? Number of Actuators = Dual
- ? Illuminated = No
- ? Dust Proof = No
- ? Support Bracket = Without
- ? Snap Action = Without

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

**Conditions for Usage:**

- ? Temperature Rating = Standard

**Packaging Related Features:**

- ? Packaging Method = Loose Piece

**Other:**

- ? Brand = Alcoswitch