

5-1825136-2 Product Details

Share | Print | Email



5-1825136-2

TE Internal Number: 5-1825136-2
 Active

Toggle Switches

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- A Series
- Single Pole - Double Throw Configuration (Pole-Throw)
- Current Rating = 0.4 VA A
- Mount Style = Solder
- Termination Type = Wire Lugs

[View all Features](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

| Documentation & Additional Information | |
|--|---|
| <p>Product Drawings:</p> <ul style="list-style-type: none"> • GEMINI A SERIES TOGGLE SWITCH, SINGLE POLE, 2 POSITI... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • SWITCHES_CORE_PROGRAM_CATALOG (PDF, English) • GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5 (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available | <p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Additional Product Images:</p> <ul style="list-style-type: none"> • Product Photo <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling |

[List all Documents](#)

| Product Features (Please use the Product Drawing for all design activity) | |
|---|--|
| <p>Product Type Features:</p> <ul style="list-style-type: none"> • Series = A • Configuration (Pole-Throw) = Single Pole - Double Throw • Termination Type = Wire Lugs <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Current Rating (A) = 0.4 VA <p>Termination Features:</p> <ul style="list-style-type: none"> • Seal Type = Terminal Seal (epoxy) <p>Body Features:</p> <ul style="list-style-type: none"> • Mount Style = Solder <p>Contact Features:</p> <ul style="list-style-type: none"> • Contact Plating = Gold | <p>Housing Features:</p> <ul style="list-style-type: none"> • Toggle Actuation = Vertical • Toggle Style = Large with Bushing • Toggle Length (mm [in]) = 12.40 [0.490] • Process Sealed = No • Bushing Style = Threaded • Bushing Type = 1/4-40 <p>Configuration Features:</p> <ul style="list-style-type: none"> • Operating Function = On On <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant <p>Other:</p> <ul style="list-style-type: none"> • Brand = Alcoswitch |

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

