

## 1825261-1 Product Details

Have a Question?

[Chat with a Product Information Specialist](#)



[Chat with a Product Information Specialist](#)



1825261-1

TE Internal Number: 1825261-1

[Active](#)

### Slide Switches

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

**Product Highlights:** [onlinecomponents.com](#)  
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

- 2 Positions
- Double Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Top
- Actuator Color = Black
- MSS Series

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [SLIDE SWITCH, MSS 2200 SERIES, VERTICAL](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Double Throw
- Actuator Style = Top
- Mount Angle = Vertical
- Terminal Configuration = Standard
- Grade = Instrumentation
- Termination Type = PC
- PCB Mount Retention = With

#### Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

#### Body Related Features:

- [Number of Positions](#) = 2
- Actuator Color = Black
- Series = MSS
- Mount Style = Through-Hole
- PCB Tail Length (mm [in]) = 5.33 [0.210]
- PCB Mount Retention Type = Guide Posts
- Actuator Length (mm [in]) = 2.30 [0.090]
- Actuator Material = Polyester
- Actuator Travel = 2.00 [.079]

#### Contact Related Features:

- Contact Plating = Silver

#### Housing Related Features:

- UL Flammability Rating = UL 94V-0

#### Configuration Related Features:

- Threaded Case = Without
- Number of Actuators = Single

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Identification Marking:

- Stamped Marking = With

#### Other:

- Brand = Alcoswitch

BOOKMARK

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

### Follow Us On:



### Visit Us On:

