

1

2

3

4

5

6

7

A

B

C

D

E

F

G

H

A

B

C

D

E

F

G

H

Specifications:

Material:

Housing: Poly Carbonate(PC) UL94V-2
 Contact: Phosphor Bronze with 2 prongs
 Plating: 6u" gold plated
 100u" Nickel under plated
 Operating temperature: -40°C to +125°C

Electrical:

Current rating: 250V AC max. at 2A
 Dielectric: 500V AC
 Insulation resistance: 500MΩ
 Termination resistance: 35mΩ max after environmental tests
 Tensile strength: 20 LBS (89N) min.
 Durability: 500 mating cycles

Complies with FCC68/F

② Wire gauge: 30AWG-24AWG Stranded wire
 Cable OD size: round cable 2.0~3.5mm
 Wire size: 0.95±0.05mm

RoHS compliant
 Unit: mm

Scale	Free					Date	Name	Customer-No.
TOLERANCE						Drawn	04.06.2014	Joanna
X.X	±0.2					Approved	03.04.2019	Amy
X.XX	±0.10							
X.XXX	±0.05	②	Add cable wire size information	03.04.2019	Amy			
DIM	TOL	①	Update drawing	12.06.2016	Joanna	ASSMANN WSW components		
X.°	±3°	③	Drawn	04.06.2014	Joanna			
X.X°	±1.0°					Replace		ASSMANN WSW-No. A-MO 4/4-SR
Angle	TOL	Id.	Modification	Date	Name	Drawing-No. ASS 6400 CO		rev02
						Sheet		

1

2

3

4

5

6

7