












NOTES	
-	ON MAIN VIEW ASSEMBLY 33254221 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 2 WAY 2.8 FEMALE CONNECTOR ASM DWG-NO.: 33253564 - FIXING SLIDE APTIV DWG-NO.: 33329557 (HT DWG-NO.: 17-1455-001-CSG) - BACKSHELL 90 DEG APTIV DWG-NO.: 33365444 (HT DWG-NO.: 17-2274-001-CSG) - BACKSHELL 180 DEG APTIV DWG-NO.: 33365244 (HT DWG-NO.:17-1454-001-CSG) - ROTARY BACKSHELL 90 DEG APTIV DWG-NO.: 35024558 (HT DWG-NO.: 18-0195-001-CSG) - ROTARY BACKSHELL 180 DEG APTIV DWG-NO.: 35024559 (HT DWG-NO.: 17-0598-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35426243 (HT DWG-NO.: 17-2269-001-CSG)
-	MATING TERMINAL SYSTEM: - 2.8 TERMINAL DWG-NO.: 13548085 MAX WIRE CROSS SECTION: 2.5MM²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK



POSITION	1				2		3	4
	HOUSING PANEL MOUNT				SECONDARY LOCK		SL SEAL	FIXING SEAL
MATERIAL	PBT GF30 FR17				PBT GF30		LSR 50 SHORE	LSR 70 SHORE
COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE
PART-NO.:	33248832	33248986	33248998	33249029	33344625	33344626	33344627	33344634
-	---	---	---	---	---	---	---	---
-	1	---	---	---	---	---	---	---
-	---	1	---	---	---	---	---	---
-	---	---	1	---	---	---	---	---
-	---	---	---	1	---	---	---	---
-	---	---	---	---	1	---	---	---
-	---	---	---	---	---	1	---	---
-	---	---	---	---	---	---	1	---
-	---	---	---	---	---	---	---	1
-	---	---	---	---	---	---	---	---



ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33254221	01	CODE A	ALL PARTS V0 / 15.5
33254220	01	CODE B	
33254108	01	CODE C	
33254107	01	CODE D	
33344850	01	CODE A	ALL PARTS NVO / 15.1
33344852	01	CODE B	
33344868	01	CODE C	
33344877	01	CODE D	

SHEET METAL THICKNESS	FIXING SLIDE APTIV/HT PART-NO.:	COLOR
-	PBT GF30 FR17	PBT GF30
1MM	33366529	33366527
1.5MM	33366530	33366521
2MM	33366531	33366520
2.5MM	33329558 / 151-02344	33344019 / 151-02345
3MM	33329560 / 151-2348	33344602 / 151-02349
3.5MM	33329561 / 151-02352	33344600 / 151-02353
4MM	33366534	33366276



DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART
FROM	> 0	> 20
TO	> 20	> 30
	> 30	> 70
	> 70	> 100
	> 100	> 150
	> 150	> 200
	> 200	> 250
	> 250	> 300
	> 300	> 400

DWG STATUS		ZONE		REVISION HISTORY		AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG					
250C18	R	01	AA		INITIAL RELEASE		K.FAR	P.NAJ	M.GRU
14MR19	R	01	AA		REFERENCE HELLERMANN TYTON DWG-NO. ADDED REFERENCE HELLERMANN TYTON PART-NO. ADDED		K.FAR	M.GRU	K.PIT
300C19	R	01	AB		PROTECTION CAP APTIV DWG-NO.: 35426243 WAS 35274873 PART AVAILABILITY FOR PART NUMBERS 33344850, 33344852, 33344868, 33344877 UPDATED		P.NAJ	M.GRU	
280C20	R	01	AC		HT DWG-NO: 18-0195-001-CSG WAS 17-0195-001-CSG		P.NAJ	M.GRU	



DWG TYP		PART DRAWING		DISTR CODE	
WEIGHT (GR)		SEE CHART			
VOLUME (CM³)		---			
ROUTING					
UNLESS OTHERWISE SPECIFIED					
GENERAL TOLERANCES ACCORDING TO: SEE CHART					
GD&T ACCORDING TO: ISO 1101					
REFERENCE					
FIRST ANGLE PROJECTION					
DO NOT SCALE					
USE MATH DATA					
CONNECTION SYSTEMS KRAKOW, POLAND COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED. TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA PEŁNE INFORMACJE POWIĘLANE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEJKOLWIEK ICH ZAWARTOŚCI, BEZ NADANIA WYRAŻNYCH UPRAWNIEN, JEST ZABRONIONE					
DR	K.FARON	DATE	240C18		
APVD1	P.NAJDUCH		250C18		
APVD2	M.GRUDZEWSKI		260C18		
APVD3					
APVD4					
APVD5					
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKREŚLA APTIV 10949001					
MATERIAL					
SEE CHART					
DRAWING NAME					
2 WAY 2.8 PANEL MOUNT CTCS MALE ASSEMBLY					
DRAWING NUMBER					
33254106					
SIZE	A1	SCALE	2:1	FRAME NO	1 OF 1
SHEET NO	1 OF 1	STG	R	REV	01
N/P	AC				