





12	11	10	9	8	7	6	5	4	3	2	1
NOTES											
- ON MAIN VIEW ASSEMBLY 33285118 SHOWN (CODE A)											
- DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION											
ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY											
MATING PARTS: - 2 WAY 6.3 FEMALE CONNECTOR ASM DWG-NO.: 35153949 - FIXING SLIDE APTIV DWG-NO.: 33294397 (HT DWG-NO.: 17-1458-001-CS6) - BACKSHELL 90 DEG APTIV DWG-NO.: 35024554 (HT DWG-NO.: 17-2275-001-CS6) - BACKSHELL 180 DEG APTIV DWG-NO.: 35024538 (HT DWG-NO.: 17-1461-001-CS6) - PROTECTION CAP APTIV DWG-NO.: 35428682 (HT DWG-NO.: 17-2271-001-CS6)											
MATING TERMINAL SYSTEM: - 5.8 TERMINAL DWG-NO.: 10857383 MAX WIRE CROSS SECTION: 6.0MM²											
1 APTIV LOGO											
2 MATERIAL NAME ACCORDING TO VDA 260											
3 DATE INSERT											
4 TOOL CAVITY NUMBER											
5 INDEX REPLACEMENT INSERT											
6 PART CAVITY NUMBER											
7 MOVING DISTANCE OF SECONDARY LOCK											








ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33285118	01	CODE A	ALL PARTS VO / 23,95
33341143	01	CODE B	
33341144	01	CODE C	
33341145	01	CODE D	
33346220	01	CODE A	ALL PARTS NVO / 23,3
33347781	01	CODE B	
33347782	01	CODE C	
33347783	01	CODE D	

POSITION	1				2		3	4
NAME	HOUSING PANAL MOUNT				SECONDARY LOCK		SL SEAL	FIXING SEAL
MATERIAL	PBT GF30 FR17				PBT GF30 FR17		LSR 50 SHORE	LSR 70 SHORE
COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE
PART-NO.:	33282970	33295516	33295350	33295348	33346024	33347366	33347365	33347364
-	---	---	---	---	---	---	---	---
-	1	---	---	---	---	---	---	---
-	---	1	---	---	---	---	---	---
-	---	---	1	---	---	---	---	---
-	---	---	---	1	---	---	---	---
-	---	---	---	---	1	---	---	---
-	---	---	---	---	---	1	---	---
-	---	---	---	---	---	---	1	---
-	---	---	---	---	---	---	---	1




MOUNTING BRACKET THICKNESS	FIXING SLIDE APTIV/HT PART-NO.:		COLOR
-	PBT GF30 FR17	PBT GF30	-
1MM	35065351	35065358	NATURAL
1.5MM	35065364	35065366	GRAY
2MM	35065367	35065368	BLUE
2.5MM	33282490 / 151-02370	33344869 / 151-02371	RED
3MM	33341422 / 151-02374	33344870 / 151-02375	YELLOW
3.5MM	33341423 / 151-02378	33344871 / 151-02379	GRAY
4MM	35065369	35065353	GREEN



DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART
FROM 1 TO	> 0	> 20
TO	> 20	> 30
	> 30	> 70
	> 70	> 100
	> 100	> 150
	> 150	> 200
	> 200	> 250
	> 250	> 300
	> 300	> 400
1) DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED	
	±0.15	±0.2
	±0.3	±0.4
	±0.5	±0.6
	±0.8	±1
	±1.2	±1.2
THEORETIC DIM	ANGULAR TOLERANCE +2°	

DWG STATUS				ZONE	REVISION HISTORY		AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG		INITIAL RELEASE		P.BAL	P.NAJ	M.GRU
19NO18	R	01	AA		G10 E9	REFERENCE HELLERMANN TYTON DWG-NO. ADDED REFERENCE HELLERMANN TYTON PART-NO. ADDED		K.FAR	M.GRU	K.PIT
14MR19	R	01	AA		G10 E9	PROTECTION CAP APTIV DWG-NO.: 35428682 WAS 35274876 PART AVAILABILITY FOR PART NUMBERS 33346220, 33347781, 33347782, 33347783 UPDATED		P.NAJ	M.GRU	

SCALE 1:1



• APTIV •

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE POWELANE, ROZPOWIECZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIAZANYCH Z NIM DANYCH CAD, JAK ROWNIEZ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAZNYCH UPRAWNIEN, JEST ZABRONIONE

DR	P.BALAJI	DATE
APVD1	P.NAJDUCH	18NO18
APVD2	M.GRUDZEWSKI	20NO18
APVD3		
APVD4		
APVD5		

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTORNIE PRZETWORZONE OKRESLA APTIV 10949001

MATERIAL
SEE CHART

DRAWING NAME
2 WAY 6.3
CTCS PANEL MOUNT MALE ASSEMBLY

DRAWING NUMBER			
35153946			
SIZE	SCALE	FRAME NO	SHEET NO
A1	2:1	1 OF 1	1 OF 1
STG	REV	N/P	AB
R	01	AB	