

Industrial grade portable GFCIs

Industrial grade 20A portable GFCIs

Product description

2-pole, 3-wire grounding
20A, 120V/AC; 20A, 240V/AC



GFI12M1NN



GFI12M133

20A portable GFCIs, inline series



Rating A	V/AC	NEMA	NEMA type	Connector style	Cord length	Cord gauge	Catalog no.*
20	120	N/A	4X	Flying leads - field wireable	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI12M1NN
				Flying leads - field wireable	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI12M2NN
				Flying leads - field wireable	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI12M4NN
				Flying leads - field wireable	50' (15.24m)	12/3 AWG	<input type="checkbox"/> GFI12M6NN
20	240	N/A	4X	Flying leads - field wireable	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI22M1NN
				Flying leads - field wireable	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI22M2NN
				Flying leads - field wireable	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI22M4NN
				Flying leads - field wireable	50' (15.24m)	12/3 AWG	<input type="checkbox"/> GFI22M6NN

*Automatic reset GFCIs are also available. When ordering automatic portable GFCIs replace "M" in catalog number with "A". Example: GFI12A1NN = Automatic; GFI12M1NN = Manual

Inline series - molded plug & connector



Rating A	V/AC	NEMA	NEMA type	Connector style	Cord length	Cord gauge	Catalog no.
20	120	5-20	4X	Molded straight blade	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI12M133
			4X	Molded locking	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI12M144
20	240	L6-20	4X	Molded locking	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI22M144

*Automatic reset GFCIs are also available. When ordering automatic portable GFCIs replace "M" in catalog number with "A". Example: GFI12A133 = Automatic; GFI12M133 = Manual

Accessories for 20A portable GFCIs

Description	Catalog no.	
20A 125V/AC NEMA 5-20 watertight plug	<input type="checkbox"/> 14W33	•
20A 125V/AC NEMA 5-20 watertight connector	<input type="checkbox"/> 15W33	•
Standard depth portable outlet box with flip lids	<input type="checkbox"/> WD3059-DDN	•
20A 125V/AC NEMA 5-20 duplex straight blade receptacle - black	<input type="checkbox"/> BR20BK	•
20A 125V/AC NEMA L5-20 industrial receptacle	<input type="checkbox"/> CWL520R	•
20A 125V/AC NEMA 5-20 duplex straight blade corrosion resistant receptacle - yellow	<input type="checkbox"/> AH5362CRY	•



14W33



15W33



WD3059-DDN



BR20BK



CWL520R



AH5362CRY

Specification information: Specification grade 20A portable GFCIs: H-18

Compliances, specifications and availability are subject to change without notice



Indicates NAFTA compliant - Page Q-30