

Specifications

Eaton AHCL1620P

Eaton Arrow Hart Color Coded Locking Plug, #14-8 AWG, 20A, Industrial, 480 V, Back, Red, Black, Ultra grip, Nylon, L16-20, Three-pole, Four-wire, Nylon, 0.38 - 1.16" (9.5 - 29.5mm), -40°C (w/o impact) to 60°C (-40°F to 140°F)

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Arrow Hart Color Coded Locking Plug |
| CATALOG NUMBER | AHCL1620P |
| UPC | 032664755743 |
| PRODUCT LENGTH/DEPTH | 2.13 in |
| PRODUCT HEIGHT | 2.92 in |
| PRODUCT WIDTH | 2.3 in |
| PRODUCT WEIGHT | 0.4 lb |
| COMPLIANCES | RoHS Compliant NAFTA |
| CERTIFICATIONS | cULus Listed NOM |



Powering Business Worldwide

Product specifications

| | |
|------------------------------|------------------------------|
| SPECIAL FEATURES | Voltage Color Coding |
| TYPE | Locking Plug |
| AMPERAGE RATING | 20A |
| VOLTAGE RATING | 3Ø 480 V |
| APPLICATION | Industrial |
| WIRING METHOD | Back |
| NUMBER OF WIRES | 4 |
| NUMBER OF POLES | Three-pole |
| COLOR | Red Black |
| CORD DIAMETER | 0.38-1.16 in (9.5-29.5 mm) |
| MATERIAL | Nylon |
| OPERATING TEMPERATURE | -40 to 60 °C (-40 to 140 °F) |
| ALLOWABLE WIRE SIZE | #14-8 AWG |
| NEMA CONFIGURATION | L16-20 |
| TORQUE RATING | 14-16 lbf-inch |
| DESIGN TYPE | Ultra grip |
| FACE/BODY MATERIAL | Nylon |

Resources

| | |
|--------------------------------------|--|
| MULTIMEDIA | Eaton Arrow Hart color coded locking devices |
| SPECIFICATIONS AND DATASHEETS | Arrow Hart color coded industrial grade L16-20 locking devices spec sheet Eaton Specification Sheet - AHCL1620P |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

