

Specifications



Powering Business Worldwide

Eaton SGFD20W

Eaton Blankface GFCI,Self-test,#14 - 10
AWG,20A,Residential,Commercial,Flush,125
V,GFCI,Back and side
wire,White,Brass,Blankface,Thermoplastic,Two-
pole,Three-wire,Two-pole, three-wire,
grounding

General specifications

PRODUCT NAME	Eaton blankface GFCI
CATALOG NUMBER	SGFD20W
UPC	032664750069
PRODUCT LENGTH/DEPTH	2.041 in
PRODUCT HEIGHT	4.751 in
PRODUCT WIDTH	2.97 in
PRODUCT WEIGHT	0.01 lb
CERTIFICATIONS	cULus Listed NOM

Product specifications

DEVICE TYPE	Receptacle Blankface
TYPE	Self-test
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CIRCUIT INTERRUPTER TYPE	GFCI
CONTACT MATERIAL	Brass
APPLICATION	<ul style="list-style-type: none">• Residential• Commercial
WIRING METHOD	Back and side wire
ALLOWABLE WIRE SIZE	#14 - 10 AWG
NEMA CONFIGURATION	5-20R
TORQUE RATING	16 lbf-inch
NUMBER OF WIRES	Three-wire
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
COLOR	White
FACE/BODY MATERIAL	PVC Thermoplastic
RECEPTACLE TYPE	Two-pole, three-wire, grounding

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

INSTALLATION INSTRUCTIONS [Installing and testing a GFCI receptacle instruction sheet](#)

MULTIMEDIA [What is a Ground Fault Circuit Interrupting \(GFCI\) receptacle?](#)

[Eaton Specification Sheet - SGFD20W](#)

SPECIFICATIONS AND DATASHEETS [Arrow Hart specification grade GFCI receptacles spec sheet](#)

[Arrow Hart self-test GFCI receptacles with audible alarm spec sheet](#)



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.