



Product: [8305](#) 

RS-232, Low Cap, #22-5pr, SR-PVC, O/A Foil+Braid, PVC Jkt, CMG

Product Description

Computer EIA RS-232 Cable, 22 AWG stranded (7x30) tinned copper conductors, semi-rigid PVC insulation, 5 twisted pairs, overall Beldfoil® (100% coverage) + tinned copper braid shield (65% coverage), PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	RS-232 Extended Distance Applications; Computer Communications; Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Panel Wiring
------------------------	---

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Pairs
Pair(s)	22	7x30	TC - Tinned Copper	5

Conductor Count:	10
------------------	----

Insulation

Element	Material	Nominal Wall Thickness
Pair(s)	S-R PVC - Semi-Rigid Polyvinyl Chloride	0.011 in

Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Alum / Poly	Beldfoil®	100 %
Braid	2	TC - Tinned Copper		65 %

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.322 in	0.035 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
15 Ohm/1000ft	4.8 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
35 pF/ft	63 pF/ft

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
60 ns/100m	60 %

Current

Max. Recommended Current [A]
2.1 Amps per conductor @ 25°C A

Voltage

UL Description	UL Voltage Rating
CMG	300 V
UL AWM 2464	300 V

Temperature Range

UL Temp Rating:	80°C (UL AWM 2464)
Operating Temp Range:	-30°C to +80°C

Mechanical Characteristics

Bulk Cable Weight:	63 lbs/1000ft
Min Bend Radius/Minor Axis:	3.25 in

Standards

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	2464
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT4
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
8305 060100	Chrome	Reel	100 ft	612825202851
8305 060500	Chrome	Reel	500 ft	612825202875
8305 0601000	Chrome	Reel	1,000 ft	612825202868
8305 0605000	Chrome	Reel	5,000 ft	612825202882

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.