



Product: [9439](#)

Electronic, 7 C #20 Str TC, PVC Ins, PVC Jkt, CMG

Request Sample

Product Description

Electronic, 7 Conductor 20AWG (7x28) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
20	7x28	TC - Tinned Copper	7

Conductor Count: 7

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.015 in

Color Chart

Number	Color
1	White
2	Red
3	Green
4	Brown
5	Blue
6	Orange
7	Black

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.26 in	0.032 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
10.7 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
27 pF/ft

Current

Max. Recommended Current [A]
2.8 Amps per conductor @ 25°C A

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2464)
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	50 lbs/1000ft
Max Recommended Pulling Tension:	86 lbs
Min Bend Radius/Minor Axis:	2.75 in

Standards

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	UL Style 2464 (300 V 80°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Footnote
9439 060100	Chrome	612825249146	
9439 0601000	Chrome	612825249153	C
9439 060500	Chrome	612825249160	C
9439 0605000	Chrome	612825249177	
9439 060U1000	Chrome	612825249122	
9439 060U500	Chrome	612825249139	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.284 Revision Date: 03-06-2020
----------------------	--

at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.