



Product: [8728](#)

Special Audio, 2 Pair 22 AWG TC, Shielded, CM

[Request Sample](#)

Product Description

Audio, 2 Pair 22 AWG stranded (7x30) TC conductors, polypropylene insulation, cabled in pairs, overall Beldfoil® shield (100% coverage), 24 AWG stranded TC drain wires, CM, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Construction Details

Conductor

Size	Stranding	Material
22	7x30	TC - Tinned Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PP - Polypropylene	0.05 in (1.3 mm)	Black & Red, White & Green

Inner Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Tape	Polyester	100%

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.028 in (0.71 mm)	0.215 in

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
17 Ohm/1000ft (56 Ohm/km)	35 pF/ft (110 pF/m)	62 pF/ft (200 pF/m)	50 Ohm	66%	2.3 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS (UL AWM Style 2717)

Mechanical Characteristics

Temperature

UL Temperature	Operating
----------------	-----------

80°C (UL AWM Style 2717)	-20°C To +80°C
--------------------------	----------------

Max. Pull Tension:	36.4 lbs (16.5 kg)
Bulk Cable Weight:	28 lbs/1000ft (42 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL1685 UL Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2717 (300 V 80°C)
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Each pair Beldfoil« shielded with individual drain wire plus a polyester film over each shield.
--------	---

History

Update and Revision:	Revision Number: 0.519 Revision Date: 12-22-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8728 060500	Chrome	Reel	500 ft	612825214687	C
8728 060U500	Chrome	UnReel	500 ft	612825214755	
8728 0601000	Chrome	Reel	1,000 ft	612825214670	C
8728 060U1000	Chrome	UnReel	1,000 ft	612825214656	
8728 0605000	Chrome	Reel	5,000 ft	612825214649	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.