



Product: [9154](#)

Electronic, 2 C #20 Str TC, PVC Ins, OS, PVC Jkt, CMG

Request Sample

Product Description

Electronic, 2 Conductor 20AWG (7x28) Tinned Copper, PVC Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	20 AWG	7x28	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.065 in (1.7 mm)	Black, Red

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.031 in (0.79 mm)	0.198 in (5.03 mm)

Overall Cable Diameter (Nominal):	0.198 in (5.03 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Max. Current
Conductor(s)	9.5 Ohm/1000ft	60 pF/ft (200 pF/m)	100 pF/ft (330 pF/m)	36 Ohm	4 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-20°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
2.0 in (51 mm)	2.0 in (51 mm)

Max. Pull Tension:	34 lbs (15 kg)
Bulk Cable Weight:	20 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.530 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9154 290500	Beige, Light	Reel	500 ft	612825224778	C
9154 290U500	Beige, Light	UnReel	500 ft	612825224754	
9154 2901000	Beige, Light	Reel	1,000 ft	612825224761	C
9154 290U1000	Beige, Light	UnReel	1,000 ft	612825224747	
9154 2905000	Beige, Light	Reel	5,000 ft	612825224785	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.