



Product: [9935](#)

RS232/423 Low Cap, #24-10c, FPE, O/A Foil+Braid, PVC Jkt, CM

Product Description

Computer EIA RS-232/423 Cable, 24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, overall Beldfoil® (100% coverage) + tinned copper braid shield (65% coverage), drain wire, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	RS-232 Extended Distance & RS-423 Applications; Computer Communications; Low Voltage Analog Signals (4-20mA, 0-10V, ...); Low Voltage Digital Control (24V, ...); Line Level Audio; Panel Wiring
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	10	24 AWG	7x32	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Color Code
Conductor(s)	PE - Polyethylene (Foam)	0.0125 in (0.318 mm)	Black, White, Red, Green, Brown, Blue, Orange, Yellow, Purple, Gray

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC
Braid	Tinned Copper (TC)	65%	

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.290 in (7.37 mm)

Overall Cable Diameter (Nominal):	0.290 in (7.37 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Velocity of Prop.	Max. Current
Conductor(s)	24 Ohm/1000ft (79 Ohm/km)	12 pF/ft (39 pF/m)	22 pF/ft (72 pF/m)	78%	1.5 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V (CM), 30 V (UL AWM 2919)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C (UL CM);80°C (UL AWM 2464)	-30°C to +80°C

Bend Radius

Stationary Min.
3.5 in (89 mm)

Max. Pull Tension:	90 lbs (41 kg)
Bulk Cable Weight:	50 lbs/1000ft (74 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL1685 UL Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2919
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Datalene® insulation features include a low dielectric constant and a low dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.
--------	--

History

Update and Revision:	Revision Number: 0.382 Revision Date: 05-05-2023
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
9935 060100	Chrome	612825264514	
9935 0601000	Chrome	612825264521	C
9935 060500	Chrome	612825264538	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.