



Product: [MDVO FACEPLATES](#)

Angled & Flush MDVO Faceplates

Product Description

Angled and Flush MDVO Faceplates are available in 1, 4, 8, & 12 Port Counts and many colors.

Technical Specifications

Product Overview

Suitable Applications:	Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800,3600, 2400 and 1200
------------------------	--

Physical Characteristics (Overall)

Height:	4.49 m
Width:	3
Depth:	107
Front Connection:	Flush
Packaging:	Individually packaged in a plastic bag.
Weight:	0.22 kg

Connectors

Materials

Material
Plastic - UL94V-0

Temperature Range

Installation Temperature Range:	-10 to 60°C
Storage Temperature Range:	-40 to 70°C
Operating Temperature Range:	-10 to 60°C

Mechanical Characteristics

Footprint/Type:	MDVO
Connector/Hardware Retention:	20 lbs

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	ACA, Bi-national Standard Listed
-----------------	----------------------------------

Related Part Numbers

Related Parts:	Compatible with 10GX, CAT6+ and CAT5E MDVO-style Modular Jacks and MDVO Multimedia Modules
----------------	--

Variants

Item #	Color	Port Count
--------	-------	------------

A0405256	Almond	1 Port
A0405295	Almond	8 Port
A0620807	Almond	12 Port
A0645268	Almond	4 Port
A0405258	Black	1 Port
A0405298	Black	8 Port
A0620809	Black	12 Port
A0645270	Black	4 Port
A0405255	Gray	1 Port
A0405294	Gray	8 Port
A0620806	Gray	12 Port
A0645267	Gray	4 Port
AX102585	Ivory	1 Port
AX102586	Ivory	8 Port
AX102587	Ivory	12 Port
AX102588	Ivory	4 Port
A0405296	White	8 Port
A0620808	White	12 Port
A0645269	White	4 Port

Product Notes

Included Parts:	blank, 6-32 screw, installation sheet
-----------------	---------------------------------------

History

Update and Revision:	Revision Number: 0.188 Revision Date: 03-04-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.