



Product: [83900](#)

Type J Thermocouple, 1 Pr #20 Sol, PVC Ins Wht, Red, Brn FEP Jkt, 300V CL3P 200C PLTC SUN RES

[Request Sample](#)

Product Description

Type J Thermocouple, 1 Pair 20AWG (Solid) Iron+Constantan, PVC Insulation Wht, Red Color Code, Brown FEP Outer Jacket, CL3P 200C PLTC SUN RES

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
20	Solid	Iron	1
20	Solid	Constantan	1

Conductor Count:	2
Total Number of Pairs:	1
Total Number of Triads:	N/A

Insulation

Material	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.01 in

Color Chart

Number	Color
Iron	White
Constantan	Red

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.076 x 0.128 in	0.012 in

Electrical Characteristics

Conductor DCR

Element	Nominal Conductor DCR
Iron	62 Ohm/1000ft
Constantan	308 Ohm/1000ft

Temperature Range

UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

Mechanical Characteristics

Bulk Cable Weight:	13 lbs/1000ft
Min Bend Radius/Minor Axis:	1.25 in

Standards

NEC/(UL) Specification:	CL3P, PLTC
Data Category:	MC 96.1-1982 Type J
ANSI Compliance:	MC 96.1-1982 Type J

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

Flammability, LSOH, Toxicity Testing

Other Flammability:	NFPA262
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
83900 001100	Brown	612825205821	100 ft	
83900 0011000	Brown	612825205838	1,000 ft	C
83900 001500	Brown	612825205845	500 ft	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.282 Revision Date: 09-10-2019
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.